

YC-76L (smart under-counter size)

High accuracy temperature controller with high sensitivity sensors, keep the temperature within $2\sim8^{\circ}$ C, Display accuracy at 0.1° C.

Refrigeration System

With renowned brand compressor and condenser, better cool performance; HCFC-FREE refrigerant ensure environmental protection & safety; Forced air cooling, auto-defrost, temperature uniformity within 3°C.

4 Human-oriented

Front opening lockable door with full height handle;

Perfect audible and visual alarms: high and low temperature alarm, sensor


failure alarm, power failure alarm, door ajar alarm;

Cabinet made of high quality steel, inner side with Aluminum plate with spraying material, durable and easy to clean;

Fitted with 2casters + (2 leveling feet);


Standard with build-in USB datalogger, remote alarm contact and RS485 interface for monitor system.





▼ Scope of Application

Suitable for storage of biological products, vaccines, drugs, reagents, etc. Suitable for use in pharmacies, pharmaceutical factories, hospitals, centers for disease prevention & control, clinics, etc.



| ~8°C Pharmacy Refrigerator | |
|--------------------------------------|---|
| Model | YC-76L |
| Cabinet Type | Upright |
| Capacity(L) | 76 |
| Internal Size(W*D*H)mm | 444*440*536 |
| External Size(W*D*H)mm | 542*566*764 |
| Package Size(W*D*H)mm | 575*617*815 |
| NW/GW(Kgs) | 41/66 |
| Performance | |
| Temperature Range | 2~8°C |
| Ambient Temperature | 16-32°C |
| Cooling Performance | 5℃ |
| Climate Class | N |
| Controller | Microprocessor |
| Display | Digital display |
| Refrigeration | |
| Compressor | 1pc |
| Cooling Method | Forced air cooling |
| Defrost Mode | Automatic |
| Refrigerant | R600a |
| Insulation Thickness(mm) | L/R:48,B:50 |
| Construction | |
| External Material | PCM |
| Inner Material | Aluminum plate with spraying |
| Shelves | 3(coated steel wired shelf) |
| Door Lock with Key | Yes |
| Lighting | LED |
| Access Port | |
| Casters | 1pc. Ø 25 mm |
| Data Logging/Interval/Recording Time | 2+ (2 leveling feet) |
| Door with Heater | USB/Record every 10 minutes / 2 years Yes |
| Backup battery | Yes |
| Alarm | |
| Temperature | High/Low temperature,High ambient temperature |
| Electrical | Power failure , Low battery |
| | |
| System | Sensor failure, Door ajar, Built-in USB datalogger failure, Communication failure |
| Electrical | |
| Power Supply(V/HZ) | 220-240~/50 |
| Power(W) | 110 |
| Power Consumption(KWh/24h) | 1.81 |
| Rated Current(A) | 0.92 |
| Accessories | |
| Standard | RS485,Remote alarm contact |

^{*}The model, parameters and performance specified in this brochure may be changed without prior notice because of product upgrading.

*There may be differences between the product images shown in this brochure and the actual products. When you are buying any product, please check the actual product.



HELAGO CZ, s.r.o. Kladská 1082, 500 03 Hradec Králové

Tel.: 495 220 229, 495 220 394

Fax: 495 220 154