



HELAGO-CZ, s.r.o.
Commercial Register maintained by the
Regional Court in Hradec Králové
Section C, File 17879
Kladská 1082
500 03 Hradec Králové 3
Company ID: 25 96 39 61, VAT: CZ 25963961
Phone: 495 220 229, 495 220 394
Fax: 495 220 154
GSM gate: 602 123 096
E-mail: info@helago-cz.cz
Web: http://www.helago-cz.cz

Vertical laminar flow clean benches offer quick operation by simple-adjustable analog control - BC-01B

Order code: **9002.AAHA6012K**



Information about product price on demand

Parameters

Inner dimensions (w x d x h) [mm]	945 x 570 x 670 [mm]
Ext. dimensions (wxdxh)	1 135 x 647 x 1 150 [mm]
Quantitative unit	pcs

Performance

- ISO class 4 (US class 10) HEPA filter for optimal protection against cross-contamination.
- 0.3 µm and larger particulates are removed with 99.99% efficiency, leak-tight HEPA filter which satisfying class 10. (US Federal Standard 209E)
(average life span of HEPA filter: 3 years - it depends on the test room conditions)
- High-quality polyester fiber pre filter (with minimal pressure loss and 85% arrestant on the A.F.I. test) for trapping larger particles and increasing the life of the main HEPA filter.
- Exclusive diffusing muffler structure forms high quality laminar flow.
- Quiet and comfortable working environment. (less than 65dB)

Convenience

- Built-in differential pressure gauge for easy checking HEPA filter condition.
- Comfortable front access to cartridge type of filters for easy replacement.
- Easy blower speed adjustment by the control panel.

- Highly durable, rust-free, and easy-to-clean grade 304 stainless steel work surface.
- The inner left side magnetic board allows some memos and small tools.

Safety

- UV-blocking and impact-resistant tempered glass door.
- If the sash is opened during UV-lamp operation, UV lamp automatically turns off to protect users.
- Lighting mode selection by 3-position toggle switch (UV / off / fluorescent) preventing harmful UV exposure.
- Smoothly sliding front door stoppable at any height for user's safety and easy transport of equipment into the workspace.
- Protection against over-current.

Optional accessories

- HEPA filter
- Stand with casters
- Pre filter