



HELAGO-CZ, s.r.o.
Commercial Register maintained by the Regional Court in
Hradec Králové
Section C, File 17879
Kladská 1082
500 03 Hradec Králové 3
Company ID: 25 96 39 61, VAT: CZ 25963961
Phone: 495 220 229, 495 220 394
Fax: 495 220 154
GSM gate: 602 123 096
E-mail: info@helago-cz.cz
Web: <http://www.helago-cz.cz>

Refraktometer RFM732-M - digital automatic

Order code: **0507.1910**



Cena bez DPH

7.410,00 Eur

Price with VAT

8.966,10 Eur

Parameters

Types of refractometers

Automatical digital refractometers

What do I measure

Sugar % (°Brix), Refractive Index RI

Serie

RFM700-M

Scale

Sugar % (°Brix) / Refractive Index (RI)

Range

0 - 100 / 1,32 - 1,54

Graduation

0.1 / 0.0001

Temperature compensation

Yes

Display

Digital

Number of ranges

2

Quantitative unit

ks

Refractometers for Food and Beverage Applications

RFM700-M Series refractometers are robust, low cost, fully automatic instruments that are ideally suited to the food, sugar and beverage industries but can also be used in many other non-food applications where temperature control is not required, for example measuring sugar (°Brix) concentrations in the food processing industry.

Automatic Temperature Control

Sample temperature stability is also important. The RFM700-M Series allows the input of a delay time that forces the operator to wait for countdown before reading, ensuring reliable results every time.

Date, time, batch & operator identifiers can be entered via the alphanumeric keypad or in the case of batch numbers, via a barcode reader connected to the instruments USB port. Over 8000 results can be saved for download. The instrument can also be connected to a printer or laboratory PC, with results being output in printed or CSV formats or as a Secure PDF.



Another new feature for the RFM700-M Series is the instruments ability to sense a sample being placed on the prism so that it can make a measurement “hands-free.” Push-button or continuous read functions are also selectable.

Key Features

- Auto-sense "hands free" measurement
- Classic red or new full colour M-Model display
- Simple audit trail (date, time & batch no.)
- Alpha-numeric keypad for easy data entry
- USB connectivity
- Flat sapphire prism surface for easy-cleaning
- Simple operation for factory environments
- Selectable read type: Continual, single, intelligent auto-sense

Software Features

- Easy to use Installation Wizard
- 7 Menu languages
- Brix and R.I. scale as standard
- Multiple user defined scales
- On-board clock
- Batch and Quality numbers
- Supervisor PIN

Specifications	RFM712-M	RFM732-M	RFM742-M
Scales			
Refractive Index	1.32 - 1.42		1.32 - 1.54
Sugar (°Brix)	0-50	1.32 - 1.54	0-100
User-defined	100	0-100	100
		100	
Resolution			
Refractive Index	0.0001	0.0001	0.00001
Sugar (°Brix)	0.1	0.1	0.01
Accuracy			
Refractive Index	±0.0001	±0.0001	±0.00005
Sugar (°Brix)	±0.1	±0.1	±0.04
Precision (Reproducibility)			
Refractive Index	± 0.00005	± 0.00005	± 0.00001
Sugar (°Brix)	± 0.05	± 0.05	± 0.01
User Scale Library	20+ pre-programmed scales including HFCS (3), Sugar (4), Honey, NaCl, Wine Must (5), Urine SG (3), Glycol (2), Urea, FSII and more; plus customer programmable user scales via PC.		
Reading Time	Minimum 4 seconds (optional time delay)		
Temperature Control	None - Automatic Temperature Compensation (ATC)		
Temperature Compensation	ICUMSA, AG, User, none		
Sample Temperature Range	0-100 °C		
Measuring Temperature Range	5-40 °C		
Temperature Sensor Accuracy	± 0.03 °C		
Sample Temperature Stability	± 0.05 °C		
Temperature Compensation			
Sucrose (°Brix)	5 - 80 °C		
AG Fluids	5 - 40 °C		
User-defined	Simple coefficient (units/ °C) or polynomial function		
Temperature Stability Checks	Delay in seconds or none		
Sample Illumination	Light Emitting Diode 589nm (100,000+ hours)		

Prism / Dish	Artificial Sapphire / Stainless Steel 316 / PEEK (spill barrier)
Prism Seal	Silicon/Resin
Interfaces	1 x USB (A), 1 x USB (B)
Power	Instrument: 24 V DC, $\pm 5\%$, <1A External PSU: 100-240V, 50-60Hz (supplied)
Humidity Range	<90% RH (non-condensing)