



HELAGO-CZ, s.r.o.
Commercial Register maintained by the Regional Court in
Hradec Králové
Section C, File 17879
Kladská 1082
500 03 Hradec Králové 3
Company ID: 25 96 39 61, VAT: CZ 25963961
Phone: 495 220 229, 495 220 394
Fax: 495 220 154
GSM gate: 602 123 096
E-mail: info@helago-cz.cz
Web: <http://www.helago-cz.cz>

**GX-32001MD - High-Capacity
Precision Balance**
Order code: **0102.GX32001MD**



Cena bez DPH

3.924,00 Eur

Price with VAT

4.748,04 Eur

Parameters

Type Balances	Industrial Bal. for Heavier Weights
Series	GX-M
Approval (Verif. ČMI)	NO
Capacity (maximum)	32200 g
Capacity / Min weigh. value [g/g]	6200/0.1 32200/1

Interface	RS-232C, USB
Specifications	IP 65, Calibration with an internal mass, Comparator function, Counting function, Animal weighing function, Percent mode function
Calibration	Internal
Weighing pan [mm]	270 × 210
Quantitative unit	ks

Features

- IP65 dust and waterproof
- Impact shock detection (ISD) providing feedback to prevent damage to the weight sensor^{*1}
- Flow rate display (FRD) that makes calculating and recording flow rates easier and more accurate^{*2}
- Shock logging function that records up to 50 adverse impact loads with a timestamp for later inspection
- Cushioning under the weighing pan to mitigate impact shocks significantly
- Flow rate comparator that indicates whether the flow rate is within the designated limits
- Tare memory function that saves the tare value in non-volatile memory
- Automatic self calibration in response to temperature changes or according to set schedules (GX-M)
- Automatic minimum weight calculation with either ECL or an actual, external weight
- Alert function to ensure that the measured quantity is not smaller than the set minimum weight
- Selectable response characteristics for trading weighing speed for higher display stability or vice versa
- User access control (UAC) that password-protects the balance from misuse
- GLP/GMP/GCP/ISO compliant output to meet documentation requirements
- Universal Flexi Coms (UFC) to customize printout content and layout ^{*3}
- Gross/Net/Tare output
- Data memory function to save weighing results, calibration results, unit masses to be used in counting mode, etc., in the device itself
- Counting mode with the Automatic Counting Accuracy Improvement (ACAI) function
- Percent mode function for target weighing or checking sample variation
- Animal weighing (average & hold) function for weighing moving objects
- Statistical calculation function (SCF) to facilitate the analysis of measurements
- Five-level comparator function with buzzer
- Auto power ON and OFF functions
- Density determination function
- Underhook for weighing a magnetic material as well as measuring density

^{*1} Patented

^{*2} For graphing weight and flow rate changes in real time, download WinCT-FRD [here](#)

^{*3} For editing and sending UFC setting commands, download WinCT-UFC [here](#)