

Data Sheet

Mixing / Overhead Stirrers



EUROSTAR 60 digital

Universally used strong laboratory stirrer for quantities up to 40 l (H₂O). It automatically adjusts the speed through microprocessor controlled technology within the speed range of 0/30 - 2000 rpm. Safety circuits installed ensures automatic cut-off in an anti-stall or overload conditions. Continuous comparison of shaft speed to desired speed is maintained and variations are adjusted automatically. This guarantees a constant speed even with changes in viscosities of the sample.

- Digital speed display
- Infinitely adjustable speed
- Push-through agitator shafts
- Overload protection
- Short-term overload operation
- Slim casing
- Quiet operation
- Error code display

Accessories: R 1342 Propeller stirrer, 4-bladed, R 1345 Propeller stirrer, 4-bladed, R 1381 Propeller stirrer, 3-bladed, R 1382 Propeller stirrer, 3-bladed, R 1385 Propeller stirrer, 3-bladed, R 1388 Propeller stirrer, 3-bladed, R 1389 (PTFE-coated) Propeller stirrer, 3-bladed, R 1311 Turbine stirrer, R 1312 Turbine stirrer, R 1313 Turbine stirrer, R 1300 Dissolver stirrer, R 1302 Dissolver stirrer, R 1303 Dissolver stirrer, R 1352 Centrifugal stirrer, R 1355 Centrifugal stirrer, R 1375 Paddle stirrer, R 1330 Anchor stirrer, R 1331 Anchor stirrer, R 3000.1 Moebius stirrer, R 3001.1 Moebius stirrer, R 3003 Spiral stirrer, R 3003.1 Spiral stirrer, R 3003.2 Spiral stirrer, R 3004 Blade stirrer, R 3004.1 Blade stirrer, R 3004.2 Blade stirrer, R 60 Keyless chuck, R 270 Boss head clamp, R 271 Boss head clamp, RH 5 Strap clamp, R 2722 H-Stand, R 2723 Telescopic stand, BC 1000 Beaker cap

Technical Data	
Stirring quantity max. per stirring position (H ₂ O) [l]	40
Motor rating input [W]	176
Motor rating output [W]	126
Motor principle	Brushless DC
Speed display	7 segment LED
Speed range [rpm]	0/30 - 2000
Viscosity max. [mPas]	50000
Output max. at stirring shaft [W]	126
Permissible ON time [%]	100
Torque max. at stirring shaft [Ncm]	60
Speed control	stepless
Setting accuracy speed [±rpm]	1
Deviation of speed measurement n > 300rpm [±%]	1
Deviation of speed measurement n < 300rpm [±rpm]	3
Stirring element fastening	chuck
Chuck range diameter [mm]	0.5 - 10
Hollow shaft, inner diameter [mm]	11
Hollow shaft (push-through - when stopped)	yes
Fastening on stand	extension arm
Extension arm diameter [mm]	16
Extension arm length [mm]	220
Speed control	electronic
Nominal torque [Nm]	0.6
housing material	alu-cast coating / thermoplastic polymer
Dimensions (W x H x D) [mm]	86 x 248 x 208
Weight [kg]	4.4
Permissible ambient temperature [°C]	5 - 40
Permissible relative humidity [%]	80
Protection class according to DIN EN 60529	IP 42
Voltage [V]	230 / 115 / 100
Frequency [Hz]	50/60
Power input [W]	176
Ident. No.	0004446000